

## 1 Moulded Fluted Grab Rails

This cost effective range of plastic grab rails have circular fixing plates supplied with a covering disc. The disc (A) is clipped over the attachment screws, creating a fully insulated handle or rail. The range consists of four rails, which are useful for the bathroom, corridors and stairways. The rails are fluted to provide better grip for wet hands.

Diameter of tubes 38mm (1½") Distance from wall 59mm (2⅓") Disc diameter 90mm (3⅔").

Code	Length	Weight
PR45712W	304mm (12")	295g
PR45716W	406mm (16")	395g
PR45718W	457mm (18")	440g
PR45724W	609mm (24")	595g




## 2 Prima Grab Bars

An innovation in safety grab rail design. The New Prima grab bar is one of the strongest and most attractive grab bars on the market. The bars feature special soft grip mouldings around the bar to reduce the risk of slipping, even with wet soapy hands. The bars are strong one piece moulded plastic with a super reinforced strength of an internal non rust aluminum tube. The ergonomical grip is comfortable and never cold to touch, unlike most metal grab bars. The straight bars can be mounted horizontally, vertically or diagonally. The two specially designed angled grab bars are ideal next to the WC, helping users with weak hand strength to rise from the seat.

Reinforced screw mounting points are concealed by colour co-ordinate plastic covers.

Size	Colour: All White	Colour: White/Mint
Straight 300mm (12")	PR60288	PR60280
Straight 400mm (16")	PR60289	PR60281
Straight 450mm (18")	PR60290	PR60282
Straight 600mm (24")	PR60291	PR60283
Angled 330mm (13")	PR60292	PR60284
Angled 400mm (16")	PR60293	PR60285



## 3 Ashby Angled Grab Bar

A grab bar which can assist the user in rising or lowering. Particularly useful in toilet assists. The angled design can be used to support the forearm to give leverage and support and the profiled design gives a pleasant non slip grip. White ABS plastic. Length 330mm (13") Depth from wall 50mm (2")

PR45218




## 4 Steel Grab Rails

Plastic coated grab rails available in three lengths. Manufactured from 25mm (1") tube. Two fixing holes with flat fixing plates.

PR45560 457mm (18")

PR45561 609mm (24")

PR45562 685mm (27")





**1 Quick Suction Rail**

The Quick Suction Rail is designed to assist your natural motion when stepping into or out of the shower/bath or when you just need that extra support. The plastic rail features ribbing along the hand rail to give additional grip and reduce the risk of slipping. The grab rail attaches to any smooth non-porous surface using suction cups meaning that no drilling is required to mount the bars. Ideal for use on tiled walls or where drilling is not possible.

Code	Total Length	Grip Length
PR45750	600mm (23.6")	400mm (15.7")
PR45751	500mm (18.5")	300mm (12")



**2 Suction Grab Handle**

The suction grab handle provides additional security for the user and is easily fixed to any smooth surface. Portable and light. Fixes to glass, baths and tiles over 115mm (4½") square. Diameter: 114mm (4½").

PR45752



**3 Stick 'n' Stay Mobility Handle**

These high quality grab handles have locking suction cups. Just flick the two pressure levers down and the handle is fixed and will not budge. To release it flip-up the leavers to effortlessly remove it. Sticks to any tiled, enamel or fibreglass surface. Special green/red indicator to show adhesion status. Extra safety and peace of mind at an affordable price.

PR45753/40 40cm long (15¾")

PR45753/50 50cm long (19¾")

## 1 Bath Tub Grab Bar

Bathtub grab bar with hand-holds for added security. Clamp can be adjusted from 76-177mm (3-7"), overall height 495mm 19.5" height above the tub 374mm (14.75").

PR45422



## 2 Premier Bath Tap Rail

The Premier Bath Tap Rail is probably the strongest most rigid and safest of any bath rail on the market. It's ready for use in a couple of minutes to provide a very stable rigid structure with multiple hand positions to help the user into the bath then lower into the water, then rise from the water and out of the bath safely and in full control. It is stylish and made of corrosion protected steel to give many years of use representing excellent value for money, promoting maximum user confidence safety, and independence.

PR45566

Max user weight  



## 3 BathTap Rail

The rail clamps firmly around the taps and provides a hinged support bar over the bath for assisting with raising and lowering. The cross bar has extended sides to sit on the rims of the bath and the rail can be folded back out of the way when not in use. Plastic end caps are fitted to help protect the bath. Max diameter of taps 76mm (3 1/8") length from taps 323mm (12 3/4") Width of cross bar 673mm (26 1/2"). Weight: 1.6 kg.

PR45563



## 4 Suction Shower Arm

Designed to compliment the use of bathing or shower boards, the shower arm allows hands free showering and washing by locating the shower head where the user requires it. With a suction clamp at the base, the shower arm can be secured to any smooth surface and is easy to position and remove. It can be moved from side to side and has a telescopic action for height adjustment from 700-1200mm (27 1/2-47 1/4").

PR45094

